

Product Datasheet

Pedestal mounted eye wash with stainless steel open bowl

STD-85G/P
STD-85GS/P

Eye/face wash facilities must be situated within 10 seconds reach of a hazard, such as the risk of a chemical spill. This pedestal mounted eye/face wash unit is quick and simple to activate in the case of an emergency. The protective dust covers lift off when the push plate is activated allowing the aerated diffusers to provide 12 litres per minute of water for a thorough decontamination.

Meets the requirements of EN15154 and ANSI Z358.1-2014.



Specifications

| MATERIALS OF CONSTRUCTION | |
|-------------------------------|--|
| PIPEWORK | Stainless steel (GS) or galvanised mild steel (G) |
| BOWL/LID | Stainless steel |
| DIFFUSERS | Chrome plated brass retaining ring, stainless steel filter mesh, plastic body |
| STANDARD FINISH | Polished brush (GS) or green powder coated (G) |
| SERVICES | |
| WATER INLET | 1 1/4" Female BSP |
| OPERATING PRESSURE | 2 to 6 BAR G / 29 to 87 PSI (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve) |
| MINIMUM FLOW RATES | 12 L per minute / 3 US gal per minute |
| AMBIENT OPERATING TEMPERATURE | |
| MINIMUM | 5C / 41F |
| MAXIMUM | 35C / 95F |
| OPERATION | |
| EYE/FACE WASH | Push plate |
| DIMENSIONS & WEIGHT | |
| DIMENSIONS (WxDxH) | 314mm (12.4in) x 535mm (21.1in) x 1154mm (45.4in) |
| WEIGHT | 10kg / 22lb |

General Arrangement Drawing

Pedestal mounted eye wash with stainless steel open bowl

STD-85G/P

STD-85GS/P

