

Product Datasheet

Pedestal mounted eye wash with ASA open bowl

STD-75G/P
STD-75GS/P

Manufactured to be quick and simple to operate in the event of an emergency, this pedestal mounted eye/face wash with open ASA bowl can be operated using the foot plate or optional foot treadle. The eye wash diffusers are protected by dust covers which “pop-off” once the unit is activated.

Pedestal pipework is available in hardwearing stainless steel or galvanised mild steel.

Meets the requirements of EN15154 and ANSI Z358.1-2014.



Specifications

MATERIALS OF CONSTRUCTION	
BOWL/LID	ASA
DIFFUSERS	Chrome plated brass retaining ring, stainless steel filter mesh, plastic body
PIPEWORK	Stainless steel (GS) or galvanised mild steel (G)
STANDARD FINISH (G)	Green powder coated (G) Polished brush finish (GS)
SERVICES	
WATER INLET	1 1/4" Female BSP
OPERATING PRESSURE	2.0 to 6 BAR G / 29 to 87 PSI (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	12 L per minute / 3 US gal per minute
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C / 41F
MAXIMUM	35C / 95F
OPERATION	
EYE/FACE WASH	Push plate (optional foot treadle control for hands free operation)
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	314mm (12.4in) x 535mm (21.1in) x 1154mm (45.4in)
WEIGHT	10kg / 22lb

General Arrangement Drawing

Pedestal mounted eye wash with ASA open bowl

STD-75G/P
STD-75GS/P

