## Heated Cabinet for use with the STD-68G

Heated cabinet intended for use with the STD-68G self-contained eye/face wash unit when positioned in locations where frost protection is required.

- Suitable for use in ambient temperatures down to -10C
- Eye wash unit can be filled while inside the cabinet via the drop down access panel
- Optional tamper proof fastenings on door and fill panel which snap in the event of an emergency or to refill
- Wall brackets included




## Specifications

MATERIALS OF CONSTRUCTION	
ENCLOSURE	Glass Reinforced Plastic (GRP) with foam insulation
COLOUR	White with green/white safety stripes and eye wash sign
SUPPORT BRACKET	Stainless-steel
SERVICES	
ELECTRICAL EQUIPMENT	ATEX Zone 1 & 2. Gas groups IIA and IIB. Temp Clase T3 (IIC available)
ELECTRICAL SUPPLY	240V, single phase, 50/60Hz
HEATING TYPE	Trace tape heated and insulated
HEATING LOAD	30 Watts
THERMOSTAT SET POINT	+15C / +59F to +5C / +41F
DIMENSIONS & WEIGHT	
DIMENSIONS - (HxWxD)	839mm (33in) x 680mm (26.8in) x 544mm (21.4in)
WEIGHT (NO OPTIONS)	Empty cabinet: 20kg
	Including STD-68G filled with water: 80kg



## Heated Cabinet for use with the STD-68G



ISOMETRIC VIEW



## www.hughes-safety.com

Hughes Safety Showers Ltd, Whitefield Road, Bredbury, Stockport SK6 2SS UK T: +44 (0)161 430 6618 E: sales@hughes-safety.com