

Pedestal mounted ASA open bowl eye wash

75GP
75GSP

Manufactured to be quick and simple to operate in the event of an emergency, this pedestal mounted eye/face wash with open ASA bowl can be operated using the foot plate or optional foot treadle. The eye wash diffusers are protected by dust covers which “pop-off” once the unit is activated.

Pedestal pipework is available in hardwearing stainless steel or galvanised mild steel.

Meets the requirements of ANSI Z358.1-2014.



Specifications

MATERIALS OF CONSTRUCTION	
BOWL/LID	ASA
DIFFUSERS	Chrome plated brass retaining ring, stainless steel filter mesh, plastic body
PIPEWORK	Stainless steel (GS) or galvanised mild steel (G)
SERVICES	
WATER INLET	1 1/4" Female BSP
OPERATING PRESSURE	2.0 to 6 BAR G / 29 to 87 PSI (higher supply pressures accommodated with the incorporation of the optional pressure reducing valve)
MINIMUM FLOW RATES	12 L per minute / 3 US gal per minute
AMBIENT OPERATING TEMPERATURE	
MINIMUM	5C / 41F
MAXIMUM	35C / 95F
OPERATION	
EYE/FACE WASH	Push plate (optional foot treadle control for hands free operation)
DIMENSIONS & WEIGHT	
DIMENSIONS (WxDxH)	314mm (12.4in) x 535mm (21.1in) x 1154mm (45.4in)
WEIGHT	10kg / 22lb

General Arrangement Drawing

Pedestal mounted ASA open bowl eye wash

75GP
75GSP

